



The Airnet II 4-Channel particle sensor makes it easy and cost-effective to monitor your cleanroom. This particle sensor offers a small footprint, unparalleled performance, and data transmission capabilities while meeting the specification of ISO 21501-4 and ISO 14644-1:2015.

Simple installation with versatile power options, the unit can be configured to accept distributed power from an in-house system, local power plug-in, or Power over Ethernet (PoE). Communication capabilities include Ethernet to interface with Pharmaceutical Net, Facility Net, or FacilityPro® software, OPC communications, Modbus communications, or optional 4-20 mA output.

Data integrity is maintained through the use of a data queue feature that continues to gather data even if network communication is lost.

To ensure proper flow conditions and vacuum system operation, these units incorporate a Dynamic Flow Sensing system that will alarm with a 15% change in flow conditions.

BENEFITS

- Proven technology provides reliable and accurate data
- Allows for immediate reaction to particle contamination events
- A low-cost solution for multipoint monitoring
- Interfaces with Facility Net, Pharmaceutical Net and FacilityPro Software for comprehensive management of cleanroom conditions
- A small footprint and flexible mounting options make it easy to install in cleanrooms and mini-environments
- A laser diode (LD) drastically reduces the need for maintenance and extends product lifecycle
- Automatic laser shutdown reduces laser failures
- Data queue maintains data integrity when communication is lost
- Optional 4-20 mA output for integration with existing systems to help you understand your environment and communicate with other systems

FEATURES

- 4 channels
- 0.2 and 10.0 μm size range
- 0.1 and 1.0 CFM flow rate
- Interfaces with object linking and embedding (OLE) for process control (OPC) communications, Modbus communications and optional 4-20 mA output
- Chemical-resistant polycarbonate (PC) enclosure
- Low sample point cost
- Small enough for use in remote locations
- Includes system validation documentation
- ISO14644-1:2015 Compliant

APPLICATIONS

- Cleanroom monitoring
- Dedicated monitoring of critical locations
- Trend analysis
- Statistical process control
- Multi-location monitoring
- Isolator monitoring



Without measurement there is no control



	201-4	301-4	310-4	501-4	510-4
Size Range (µm)	0.2, 0.3, 0.5, 1.0	0.3, 0.5, 1.0, 5.0	0.3, 0.5, 1.0, 5.0	0.5, 1.0, 5.0, 10.0	0.5, 1.0, 5.0, 10.0
Flow Rate	0.1 CFM (2.8 LPM)	0.1 CFM (2.8 LPM)	1.0 CFM (28.3 LPM)	0.1 CFM (2.8 LPM)	1.0 CFM (28.3 LPM)
Counting Efficiency	50% ± 20% for most sensitive channel. Meets ISO 21501-4 100% ± 10% at 1.5 to 2.0 times channel one size. Meets ISO 21501-4				
Zero Count	≤ 70.7 counts/m ³	≤ 70.7 counts/m ³	≤ 7.07 counts/m ³	≤ 70.7 counts/m ³	≤ 7.07 counts/m ³
Maximum Concentration ¹	5,057,310 /ft ³	4,862,798 /ft ³	702,404 /ft ³	7,437,220 /ft ³	890,371 /ft ³
Laser Source	Diode				
Laser Classification	Class 1 per EN60825 (Internally, a Class IIIB laser is used, per EN60825)				
Exterior Surface	Polycarbonate				
Dimensions (H x W x L)	3.8 x 3.6 x 5.3 in (9.6 x 8.9 x 13.5 cm)				
Weight	1.6 lb (0.73 kg)				
Sample Probe or Tubing	1/4" ID				
Flow System	External vacuum 1/4" connection Automatic laser shutoff and alarm on 15% flow variation				
Vacuum Source	> 12 in Hg required				
Power	Power over Ethernet (PoE) via PoE router (48 VDC) or PoE power injector Optional 24 VDC (0.5 A) power input				
Communication Connectors	Ethernet (Particle Measuring Systems proprietary protocol, OPC, Modbus TCP) Optional 4-20 mA (5 output channels: 4 particle data, 1 instrument status) RS-232 (configuration and diagnostic only)				
Status Indicators	Programmable status (two-color LED), Activity (one-color LED)				
Calibration	Calibration materials used are traceable to the National Institute for Standards and Technology (NIST) and meet ISO 21501-4 requirements				
Environment	Temperature: 39 – 95 °F (4 – 35 °C) Relative humidity: 5 – 95%, non-condensing				
Complies With	EU RoHS, ISO 21501-4				

¹Greater than 90% accuracy (less than 10% coincidence loss)

at maximum recommended concentration.

Airnet®, FacilityPro® and IsoAir® are registered trademarks of Particle Measuring Systems, Inc. All other trademarks are the property of their respective owners. Particle Measuring Systems, Inc. reserves the right to change specifications without notice. © 2016 Particle Measuring Systems, Inc. All rights reserved.

GERMANY



PARTICLE MEASURING **SYSTEMS**[®]

a Spectris company

5475 Airport Blvd Boulder, Colorado 80301 USA T: +1 303 443 7100, +1 800 238 1801

Instrument Service & Support T: +1 800 557 6363

HEADQUARTERS

Customer Response Center T: +1 877 475 3317 E: info@pmeasuring.com

www.pmeasuring.com info@pmeasuring.com

GLOBAL OFFICES

T: +43 512 390 500

T: +32 10 23 71 56

T: +55 11 5188 8227

T: +86 21 6113 3600

T: 33(0)1 60 10 32 96

BENELUX

BRAZIL

CHINA

FRANCE

AUSTRIA

E: pmsbelgium@pmeasuring.com

E: pmsbrazil@pmeasuring.com

E: pmschina@pmeasuring.com

E: pmsfrance@pmeasuring.com

T: +49 6151 6671 632 E: pmsgermany@pmeasuring.com E: pmsaustria@pmeasuring.com

ITALY T: +39 06 9053 0130 E: pmssrl@pmeasuring.com

JAPAN T: +81 3 5298 8175 E: pmsjapan@pmeasuring.com

KOREA T: +82 31 286 5790 E: pmskorea@pmeasuring.com

MEXICO T: +52 55 2271 5106 E: pmsmexico@pmeasuring.com NORDIC T: +45 707 028 55 E: pmsnordic@pmeasuring.com

PUERTO RICO T: +1 787 718 9096 E: pmspuertorico@pmeasuring.com

SINGAPORE T: +65 6496 0330 E: pmssingapore@pmeasuring.com

SWITZERLAND T: +41 71 987 01 01 E: pmsswitzerland@pmeasuring.com

TAIWAN T: 886-3-5525300 Ext: 301 E: pmstaiwan@pmeasuring.com